

## LMA-PM-10

*Single-mode 10 μm polarization-maintaining fiber*

- Low loss fiber from 500 to 1700 nm
- Single mode at all wavelengths
- Polarization Maintaining
- Radiation hard pure silica fiber
- Wavelength independent MFD

This polarization-maintaining single-mode fiber is optimized to exhibit low loss from 500 nm to 1700 nm while keeping an almost constant mode field diameter.

The fiber is endlessly single-mode (i.e. it has no higher order mode cut-off) and delivers pristine mode quality at all wavelengths.


This product is also available in a non polarization-maintaining version as the LMA-10

Optical properties	
Single mode cut-off wavelength*	None
Attenuation @ 532 nm	< 20 dB/km
Attenuation @ 632 nm	< 10 dB/km
Attenuation @ 1064 nm	< 5 dB/km
Mode field diameter @ 532 nm (1/e <sup>2</sup> )	8.4 ± 0.5 μm
Mode field diameter @ 1064 nm (1/e <sup>2</sup> )	8.6 ± 0.5 μm
NA @ 1064 nm (5%)	0.13 ± 0.02
Birefringence Δn @ 1064 nm	1.4 · 10 <sup>-4</sup>
Polarization Extinction Ratio**	> 18 dB
Physical properties	
Core diameter	10.0 ± 0.5 μm
Outer cladding diameter, OD	230 ± 5 μm
Coating diameter	350 ± 10 μm
Core and cladding material	Pure silica
Coating material, single layer	Acrylate
Coating concentricity	< 10 μm
Proof test level	0.33 %
Standard interfacing options	
FC/PC PM connector	0.0 ± 0.5 deg angle
FC/APC PMconnector	8.0 ± 0.5 deg angle
SMA 905	0.0 or 5.0 ± 0.5 deg angle
Collapse and cleave	0.0 ± 0.5 deg angle

All interfaces are provided with a 150 ± 25 μm sealing length of the PCF structure. PM connectors are keyed to the slow axis. Please contact us for other custom interfacing options.

\* TIA-455-80-C standard


\*\* AKA PXtalk on a 2 m sample




### Applications

- Single-mode PM short wavelength delivery
- Multi-wavelength transmission
- Mode filtering
- Single-mode PM pigtailling
- Short pulse delivery

### Typical spectral attenuation and dispersion



### Typical measured NA and MFD



LMA-PM-10-111222